



WXF688N

## Blank function gallery 1 module night

### Technical characteristics

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	29.5 mm
-------	---------

Height	45 mm
--------	-------

Width	22.5 mm
-------	---------

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	night
------------------------------	-------

Surface appearance	satin finish
--------------------	--------------

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----