



WXF689B

## Blank function gallery 2 modules pure-white

### Technical characteristics

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	24 mm
Height	45 mm
Width	45 mm

#### Capacity

Number of sockets	3
-------------------	---

#### Materials

Free area for finishing name	pure
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
Composition	other
With imprint	No