



WXF689N

Blank function gallery 2 modules night

Technical characteristics

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	24 mm
-------	-------

Height	45 mm
--------	-------

Width	45 mm
-------	-------

Capacity

Number of sockets	3
-------------------	---

Materials

Free area for finishing name	night
------------------------------	-------

Surface appearance	satın finish
--------------------	--------------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	other
-------------	-------

With imprint	No
--------------	----