



WXP0002

## Plate gallery plastic 1 gang pure-white

### Technical characteristics

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 9.3 mm

Height 88 mm

Width 92 mm

#### Capacity

Number of sockets 1

#### Materials

Free area for finishing name pure

Colour white

Surface appearance glossy

Type of surface treatment untreated

#### Installation, mounting

Mounting way horizontal

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted frame