



WXP0302

Plate gallery plastic plastic 1 gang dune

Technical characteristics

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 92 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name dune

RAL colour RAL 1013 - Oyster white

Type of surface treatment untreated

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame