



WXPS82

**IP66 Weatherproof 2G 13A Unswitched Socket**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Functions**

Overvoltage protection No

**Configuration**

Number of modules 0

**Main electrical features**

Nominal voltage 250 V AC

Rated current 13 A

**Electric current**

Rated current 13 A

**Dimensions**

Depth 88.25 mm

Height 116.5 mm

Width 146 mm

**Cover, door**

Cover Full cover plate

**Power supply**

Special power supply No special power supply

**Materials**

Colour light grey

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment untreated

**Installation, mounting**

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

**Connection**

Type of connection screw

**Cable**

Wiring

with double earth connection

---

**Equipment**

Number of socket outlets switchable

0

---

**Safety**

IK protection code against mechanical impacts

sonstige

Protection index IP

IP66

Protection

Enhanced contact protection