



WXPSS115

## IP66 Single 15A Switched Socket

### Technical characteristics

#### Functions

Overvoltage protection	No
------------------------	----

#### Configuration

Number of modules	0
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	15 A

#### Electric current

Rated current	15 A
---------------	------

#### Dimensions

Depth	88.25 mm
Height	86 mm
Width	86 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Power supply

Special power supply	No special power supply
----------------------	-------------------------

#### Materials

Colour	light grey
Surface appearance	matt
Type of surface treatment	untreated

#### Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting ; for screw fastening

#### Connection

Type of connection	screw
--------------------	-------

#### Cable

Wiring	with earth connection
--------	-----------------------

#### Equipment

**Use**

Differentiation characteristic 3 - Sales

with screw terminals

**Safety**

IK protection code against mechanical impacts

sonstige

REACH conform

Yes

RoHS conform

Yes

Protection

Enhanced contact protection