



WXPSS115

IP66 Single 15A Switched Socket

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Overtoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 15 A

Electric current

Rated current 15 A

Dimensions

Depth 88.25 mm

Height 86 mm

Width 86 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour light grey

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment untreated

Installation, mounting

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection screw

Cable

Wiring

with earth connection

Equipment

Number of socket outlets switchable

1

Use

Differentiation characteristic 3 - Sales

with screw terminals

Safety

IK protection code against mechanical impacts

sonstige

Protection index IP

IP66

REACH conform

Yes

RoHS conform

Yes

Protection

Enhanced contact protection