



WXPSS82

IP66 Weatherproof 2G 13A DP Switched Socket

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Overvoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V AC

Rated current 13 A

Electric current

Rated current 13 A

Dimensions

Depth 88.25 mm

Height 116.5 mm

Width 146 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour light grey

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment untreated

Installation, mounting

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection screw

Cable

Equipment

Number of socket outlets switchable	0
-------------------------------------	---

Safety

IK protection code against mechanical impacts	sonstige
---	----------

Protection index IP	IP66
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Protection	Enhanced contact protection
------------	-----------------------------