



WXPSS82-ME

IP66 Twin 13A Double Pole Switched Socket

Technical characteristics

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	0
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	220...230 V AC
---------------	----------------

Rated current	13 A
---------------	------

Electric current

Rated current	13 A
---------------	------

Dimensions

Depth	88.25 mm
-------	----------

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour	light grey
--------	------------

Surface appearance	matt
--------------------	------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Fixing type	With screws
-------------	-------------

Installation mode	for wall mounting ; for screw fastening
-------------------	---

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with earth connection
--------	-----------------------

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Use

Differentiation characteristic 3 - Sales

with screw terminals

Safety

IK protection code against mechanical impacts

sonstige

Protection

Enhanced contact protection