



HBW400H

### Aardlekelement P630 4P 400 A I<sub>dn</sub> 100 mA tot 10 A instelbaar

#### Technische eigenschappen

##### Elektrische Stroom

Nominale stroom	400 A
-----------------	-------

Nominale aardlekstroom I <sub>dn</sub>	100 mA, 300 mA, 500 mA, 1000 mA, 3000 mA, 10000 mA
--	--

##### Architectuur

Aantal polen	4
--------------	---

##### Veiligheid

Type aardlekbeveiliging	A HI
-------------------------	------

##### Spanning

Nominale isolatiespanning U <sub>i</sub>	500 V
--	-------

Nominale stoothoudspanning U <sub>imp</sub>	6000 V
---	--------