



Deksel Q06 200x200mm zwart voor 12mm vloerafdekking

Technische eigenschappen	
Montagevoorschriften	
Pole fastening	Nee
Add-on device	Nee
Gland plate category	
Suitable as rear panel	Nee
Suitable as side panel	Nee
Suitable for cavity floor installation	Ja
Suitable for functional integrity according to DIN 4102-12	Nee
Suitable for raised floor installation	Ja
Suitable for sub floor duct	Ja
Suitable for wet cleaning	Nee
Uitvoering	723
Zekeringskarakteristiek	
Nominal installation size	Q06
Dekselmontage	
Uitvoering deksel	5330
With cut out	Nee
Kleur	zwart
Bestandsdeel	polyamide (PA)
Materiaalgroep	kunststof
Oppervlak	
Oppervlaktebehandeling	poeder coated
Surface treatment of busbar	
Suitable for wall mounting	Nee
Inclusief railsysteemklemmen	
Uitgevoerd met	
Uitbreiding mogelijk	Nee
Invoerstukken	

Onderdelen	
Equipped with connectors	Nee
Metering exchange plate included	Nee
Pitched roof	Nee
With backside door	Nee
With bottom plate	Nee
With busbar	Nee
With carpet protection frame	Ja
With opening carpeting	Ja
With protective film	Nee
Met zuil (basis)	Nee
Keurmerken	EN50085-2-2
UL 94 classificatie	
Beschermingsgraad (IP)	
Gloeidraad test	
Halogeenvrij	Ja
Slagvastheid	IK08
Ultraviolet resistant	Nee
Vorm	
Slotted	Nee