



Deksel E09 200x253mm zwart voor 5mm vloerafdekking

Technische eigenschappen

Montagevoorschriften

Pole fastening

Nee

Add-on device

Nee

Gland plate category

Suitable as rear panel

Nee

Suitable as side panel

Nee

Suitable for cavity floor installation

Ja

Suitable for functional integrity according to DIN 4102-12

Nee

Suitable for raised floor installation

Ja

Suitable for sub floor duct

Ja

Suitable for wet cleaning

Nee

Uitvoering

722

Zekeringskarakteristiek

Nominal installation size

E09

Dekselmontage

Uitvoering deksel

5330

With cut out

Nee

Kleur

zwart

Bestandsdeel

polyamide (PA)

Materiaalgroep

kunststof

Oppervlak

Oppervlaktebehandeling

poeder coated

Surface treatment of busbar

Suitable for wall mounting

Nee

Inclusief railsysteemklemmen

Uitgevoerd met

Uitbreiding mogelijk

Nee

Invoerstukken

Onderdelen	
Equipped with connectors	Nee
Metering exchange plate included	Nee
Pitched roof	Nee
With backside door	Nee
With bottom plate	Nee
With busbar	Nee
With carpet protection frame	Ja
With opening carpeting	Ja
With protective film	Nee
Met zuil (basis)	Nee
Keurmerken	EN50085-2-2
UL 94 classificatie	
Beschermingsgraad (IP)	
Gloeidraad test	
Halogeenvrij	Ja
Slagvastheid	IK08
Ultraviolet resistant	Nee
Vorm	
Slotted	Nee