



**Lid made of PVC for slotted panel trunking DNG 20mm stone grey**

**Technical properties**

**Compatibility**

|                       |          |
|-----------------------|----------|
| Product compatibility | DN, DNG, |
|-----------------------|----------|

**Electric current**

|                     |     |
|---------------------|-----|
| Current leak stable | Yes |
|---------------------|-----|

**Dimensions**

|        |         |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

|                |       |
|----------------|-------|
| Trunking width | 20 mm |
|----------------|-------|

**Cover, door**

|              |          |
|--------------|----------|
| Lid mounting | External |
|--------------|----------|

|                  |    |
|------------------|----|
| Lid with softlip | No |
|------------------|----|

|           |       |
|-----------|-------|
| Lid width | 19 mm |
|-----------|-------|

**Materials**

|        |            |
|--------|------------|
| Colour | stone grey |
|--------|------------|

|          |     |
|----------|-----|
| Material | PVC |
|----------|-----|

|                |         |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

|                           |           |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

**Standards**

|                         |                      |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|              |    |
|--------------|----|
| Halogen free | No |
|--------------|----|

**temperatur**

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|

DN3702027030