



DNG3703707030B

Slotted panel trunking made of PVC DNG 37x37mm stone grey

Technical properties

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	37 mm
Length	2000 mm
Trunking width	37 mm
Slot width	5 mm
Tongue width	7.5 mm

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	DIN 43659
---------------	-----------

Cable

Number of wires 1,5 mm ² - 40% filling degree	48
Internal/useful cross section	1036 mm ²
Number of wires 2,5 mm ² - 40% filling degree	35
Number of wires 1,0 mm ² - 40% filling degree	67

Standards

European directive RoHs	voluntary compliance
UL 94 classification	V0

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1