



EC700

Pulses concentrator

Technical properties

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 4

Main electrical features

Rated operational voltage Ue 100 / 230 / 400 V

Electric current

Number of entry circuits 7

Dimensions

Depth of installed product 50 mm

Height of installed product 90 mm

Length 73 mm

Width of installed product 67 mm

Width 90 mm

Measurement

Type of measuring instrument digital

Installation, mounting

Mounting type din-Rail

Connection

Type of Bus connexion other

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...55 °C

Type of primary energy Current

Storage/transport temperature -20...70 °C