



EEN003

IP55

Cell for twilight switch, wall mounted

Technical properties

Dimensions

Depth of installed product	41.3 mm
Height of installed product	32 mm
Length	131.4 mm
Width of installed product	48 mm

Length

Maximum connection distance between receiver and transmitter	100m
--	------

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Connection

Conductor cross-section	0.75...4 mm ²
-------------------------	--------------------------

Cable

Wire	Cable length between twilight switch and brightness sensor max. 100 m
------	---

Settings

Delay ON	60 s
Delay OFF	80 s

Equipment

Probe type	light sensor
------------	--------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-25...70 °C

Identification

Main design line	House electronics
------------------	-------------------