



EEN003



Cell for twilight switch, wall mounted

Technical properties

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 41.3 mm

Height of installed product 32 mm

Length 131.4 mm

Width of installed product 48 mm

Lighting control

Brightness measurement range 5 / 2000 Lux

Installation, mounting

Mounting type surface-mounted

Connection

Conductor cross-section 0.75...4 mm²

Settings

Delay ON 60 s

Delay OFF 80 s

Equipment

Probe type light sensor

Safety

Protection index IP IP55

Use conditions

Operating temperature -25...70 °C

Storage/transport temperature -25...70 °C