



EG293B



Yearly time switch 2 channels, digital, 4 modules

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Number of function channels 2

Multi-phase mode suitable for multi-phase mode

Function Presence simulation ; Keylock via PIN code ; with operating hours meter ; with pulse function

Configuration

Switch mode 2 x change-over contact

Number of modules 4

Controls and indicators

Indication / display LC display with illumination

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V~

Dimensions

Depth of installed product 69 mm

Height of installed product 90 mm

Width of installed product 70 mm

Width of rail mounted device (RMD) 4 modules

Power

Power consumed 2 VA

Total power loss under IN 2 W

Loss power at full load \approx 2 W

Measurement

Running accuracy \pm 0.2 s/day

Battery

Power reserve [years] \approx 5 a

Lithium cell power reserve [years] \approx 5

Battery / storage battery with lithium coin cell battery type: CR2450

Incandescent bulbs control

Max. power with incandescent lamps	1500 W
230 V incandescent lamps and halogen lamps	max. 1500 W

Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Number of contacts	2
Type of contacts	2 changeover + 2NO
Type of connection	with QuickConnect plug-in terminals
Contact	with potential-free switching contact
Type of connection	quick connect

Settings

Number of program steps	300
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital, with programming key
Programming cycle	yearly
Programs	with random programme ; holiday programme with date activation
Programming	Programming possible without mains voltage
Time	with automatic summer/winter time change-over

Equipment

Number of channels	2
Number of switching times for on/off	300
Supply failure reserve	5 years
With holidays program	Yes

Use

Cycle	yearly
-------	--------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Key	with programming key

Use conditions

Operating temperature	-10...50 °C
Working accuracy	+ 0,2 s / 24h
Storage/transport temperature	-20...70 °C

