




EHN111



Daily time switch 1 channel, 3 modules with reserve

Technical properties

Equipment

Number of channels 1

Frequency

Frequency 50 - 60 Hz

Power

Power consumption during operation 0,50 W

230 V incandescent and halogen lamp 1100 W

Power loss at full load 1 W

Functions

Number of function channels 1

Connection

Number of contacts 1

Cross-section flexible conductor 0.5 - 6 mm²

Cross-section rigid conductor 0.5 - 6 mm²

Use conditions

Operating temperature -10 - +55 °C

Capacity

Number of modules 3

Dimensions

Height 90 mm

Width 54 mm

Depth 60 mm

Texts

Switch mode Change-over contact

Installation mode For mounting on DIN rail

Type of connection With screw terminals

Electric current

Max. power (cos phi 0,6) 3 A

Endurance

Electrical durability at nominal load in AC1
in operating cycles 50000

Voltage

Rated operational voltage U_e

230 - 240 V