



ESC225S

**Humfree Contactor 25A, 2NO, 230V~50/60Hz**

**Technical properties**

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

**Power**

Inrush power absorbed	2.5 VA
Operating consumption	2.5 VA
Total power loss under IN	5.2 W
Power loss per contact	1.5 W
Power dissipation per coil	2.2 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

**Tripping**

Time of response when opening	15 ms
Time of response when closing	25 ms

**Endurance**

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations 100000

---

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps 810 VA

Fluorescent lamps in duo circuit 1990 VA

Max. load fluorescent lamp 950 VA

---

**Incandescent bulbs control**

Max. power with incandescent lamps 1900 W

---

**Connection**

Connection cross-section of the control cable solid 1 / 10 mm<sup>2</sup>

---

**Equipment**

Can be accessorized No

---

**Use**

Local operation/hand operation No

---

**Standards**

European directive WEEE concerned

---

**Safety**

Protection index IP IP2X

---

**Use conditions**

Operating temperature -10...50 °C

Storage/transport temperature -40...80 °C