



FD72DN

Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, distribution

Technical properties

Connection

Number of conduit inlets 4

Voltage

Nominal voltage 230 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 160 A

Equipment

Number of rails 7

Number of rows 7

With lock No

Has neutral terminal block No

Has earthing terminal block Yes

Has mounting plate No

Capacity

Number of modules 168

Dimensions

Height 1200 mm

Width 550 mm

Depth 193 mm

Number of width units 24

Cover, door

Number of cabinet doors 0

Number of locks 0

Door/cover is transparent No

Materials

Material Metal, Plastic

RAL code 9010

Colour Pure white

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock