



GD104T

Mini-enclosure, GD, 4 module wide, protect. class IP30,without door

Technical properties

Voltage

Nominal voltage 230 - 230 V

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 40 A

Equipment

Number of rails 1

Number of rows 1

With lock No

Has neutral terminal block No

Has earthing terminal block No

Has mounting plate No

Capacity

Number of modules 4

Dimensions

Height 180 mm

Width 110 mm

Depth 82 mm

Number of width units 4

Cover, door

Door/cover is transparent No

Materials

Material Plastic

RAL code 9010

Colour Pure white

Safety

Protection class Isolation class II

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Locking type Without lock

Glow wire test 750 °C