



HIC416A

Motorized changeover switch 4P 160A 400V

Technical properties

Voltage

Rated operational voltage U_e 380 - 415 V

Electric current

Rated current 160 A

Rated conditional short-circuit current I_{cc}
with gl-gG fuses 40 kA

Power

Rated operational power under 400 V AC
AC1 105000 W

Architecture

Number of poles 4

Device construction type Fixed built-in

Compatibility

Suitable for distribution board Yes