



HIC416A

## Motorized changeover switch 4P 160A 400V

### Technical properties

#### Architecture

Type of order	Not applicable
Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

#### Functions

Reversing switch	Yes
------------------	-----

#### Controls and indicators

Motor drive integrated	Yes
------------------------	-----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

#### Electric current

Rated current	160 A
Short-circuit current with gI-gG fuses	40 kA
Rated short-time withstand current 1s	4 kA
Rated operational current in AC23 category A	125 A

#### Power

Total power loss under IN	22.5 W
Power loss per pole at In	7.5 W
Contact rating with 400 V in AC1	105 kW

#### Cover, door

Interlockable	Yes
---------------	-----

#### Installation, mounting

Tightening torque	4 - 4.4 Nm
-------------------	------------

#### Connection

Type of connection	with screw
--------------------	------------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

---

Number of auxiliary contacts as change-over contact	0
---	---

---

Motor drive optional	No
----------------------	----

---

**Standards**

---

Standard text	IEC 60947-3 ; IEC 60947-6
---------------	---------------------------

---

**Safety**

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----