



HTC320H

## COMMUNICATION Module with inputs and outputs

### Technical properties

#### Configuration

Number of modules

2

#### Main electrical features

Type of supply voltage

DC

#### Voltage

Input voltage

24 V DC

Operating voltage

24 V DC

Output voltage

24...48 V DC

#### Electric current

Input current

max. 15 mA

Output current

max. 50 mA

#### Equipment

Number of digital inputs

2

#### Standards

European directive RoHS

compliant

#### Use conditions

Operating temperature

-25...70 °C

Storage/transport temperature

-35...70 °C