



HTD210H

Display for Energy MCCB

Technical properties

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

Rated operational voltage in DC	24 V
---------------------------------	------

Dimensions

Cut-out (W x H)	92 mm
-----------------	-------

Power

Power absorbed	2 W
----------------	-----

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-10...55 °C
-------------------------------	-------------