



HTD210H

Display for Energy MCCB

Technical properties

Voltage

Rated operational voltage in DC 24 V

Dimensions

Cut-out (W x H) 92 mm

Power

Power absorbed 2 W

Standards

European directive WEEE concerned

Use conditions

Operating temperature -10...55 °C

Storage/transport temperature -10...55 °C