



HXA028H

**Alarm contact-Low level NO-NC right side (x630/P630)**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Main electrical features**

Rated operational voltage Ue	125 V
------------------------------	-------

**Voltage**

Rated impulse withstand voltage	1500 V
---------------------------------	--------

Rated operational voltage in DC	30 V
---------------------------------	------

**Electric current**

Rated current	0.1 A
---------------	-------

**Power**

Total power loss under I <sub>N</sub>	3 W
---------------------------------------	-----

**Connection**

Type of contacts	1 changeover
------------------	--------------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	1
---	---

Number of auxiliary contacts as fault signal	2
--	---

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

European directive WEEE	concerned
-------------------------	-----------