



HXA028H

**Alarm contact-Low level NO-NC right side (x630/P630)**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Main electrical features**

Rated operational voltage Ue 125 V

Type of supply voltage AC/DC

**Voltage**

Rated impulse withstand voltage 1500 V

Rated operational voltage in DC 30 V

**Electric current**

Rated current 0.1 A

**Power**

Total power loss under IN 3 W

**Connection**

Type of contacts 1 changeover

Type of connection quick connect

**Equipment**

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 1

Number of auxiliary contacts as fault signal 2

**Standards**

European directive RoHS voluntary compliance