



HXB042H

Motor operator x250 230-240VAC

Technical properties

Architecture

Type of order motor drive

Main electrical features

Rated operational voltage Ue 220 / 240 V

Type of supply voltage AC

Frequency 50/60 Hz

Voltage

DC control voltage 0 V

Command voltage AC 230 / 240 V

Rated operational voltage in DC 0 V

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under IN 24 W

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m