



HXB042H

**Motor operator x250 230-240VAC**

**Technical properties**

**Main electrical features**

Rated operational voltage Ue	220 / 240 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

DC control voltage	0 V
Command voltage AC	230 / 240 V
Rated operational voltage in DC	0 V

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	24 W
---------------------------	------

**Standards**

European directive RoHS	voluntary compliance
European directive WEEE	concerned

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m