



HXE013H

**UVR 110-120V AC (h800-h1000-h1600)**

**Technical properties**

**Voltage**

|                    |             |
|--------------------|-------------|
| DC control voltage | 0 V         |
| Command voltage AC | 110 / 120 V |

**Frequency**

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

**Power**

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 1.6 W |
|---------------------------|-------|

**Equipment**

|   |   |
|---|---|
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |
| Number of auxiliary contacts as change-over contact     | 0 |

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Use conditions**

|  |        |
|--|--------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3      |
| Altitude   | 2000 m |