



HXF040H

Motor operator h1250-h1600 24V DC

Technical properties

Architecture

Type of order motor drive

Main electrical features

Rated operational voltage Ue 0 V

Type of supply voltage DC

Voltage

DC control voltage 24 V

Command voltage AC 0 V

Rated operational voltage in DC 24 V

Frequency

Frequency 0 Hz

Power

Total power loss under IN 24 W

Standards

European directive RoHS voluntary compliance

Use conditions

Degree of pollution according to IEC 60664 /
 IEC 60947-2 3

Altitude 2000 m