



HYA006H

### Collar terminal x160 Al 4P

#### Technical properties

##### Architecture

Number of poles 4 P

##### Electric current

Rated current 160 A

##### Installation, mounting

Tightening torque 10Nm

##### Connection

Connection cross-sect. flexible conductor 35 / 70mm<sup>2</sup>

Connection cross-sect. rigid cable 35 / 70 mm<sup>2</sup>

Conductor cross-section 35...70 mm<sup>2</sup>

##### Cable

Cable Material Cu / Al

##### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

##### Use conditions

Degree of pollution according to IEC 60664 /  
IEC 60947-2 3

Altitude 2000 m