



HYW014H

Spread terminal extension x630/P630 3P (up to 630A)

Technical properties

Architecture

Number of poles	3 P
Type of pole	3 P

Electric current

Rated current	630 A
---------------	-------

Power

Total power loss under IN	19 W
Power loss per pole at In	6.35 W

Installation, mounting

Tightening torque	18Nm
-------------------	------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes