



JVC0EXTDW

Invicta Ext Box-2 rows x 18P DIN WH (WH)

Technical properties

Configuration

Number of modules	18
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	140 mm
Depth of installed product	140 mm
Internal depth	138 mm
Height of installed product	350 mm
Width of installed product	480 mm
Width in division units	9
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.2 mm
Identification of protection index	30
Interlockable	No
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Surface appearance	satin finish

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	2
Quantity of rails	2
Number of openings for flange plates	1
Extension possible	Yes

Standards

Approvals	AS/NZS 61439-3
-----------	----------------

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Fire resistance	-
