



JVC2400S16TW

160A TPN board, INVICTA, 24P Chassis, ISO-STD-GR

Technical properties

Architecture

Number of poles of the main switch	3
------------------------------------	---

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	16
-------------------	----

Main electrical features

Rated operational voltage Ue	415 V
Nominal voltage	400 V
Frequency	50/60 Hz

Electric current

Rated current	160 A
---------------	-------

Dimensions

Insertion depth	117 mm
Depth of installed product	135 mm
Internal depth	115 mm
Height of installed product	800 mm
Width of installed product	480 mm
Thickness of sidewall material	1.2 mm

Cover, door

Interlockable	No
Number of keylock of the door	1
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey

Connection

Number of accessible phases	24
-----------------------------	----

Equipment

With energy meter	No
Quantity of rails	1
Can be accessorized	Yes

With bell transformer	No
Extension possible	Yes
With socket	No
Safety	
IK protection code against mechanical impacts	05
Protection class	isol.class I
Glow wire test	according to AS/NZS 61439-1