



JVC3600S25TW



**250A TPN board, INVICTA, 36P Chassis, ISO-STD-GR**

**Technical properties**

**Architecture**

Number of poles of the main switch 3

**Functions**

Overvoltage protection No

**Configuration**

Number of modules 16

**Main electrical features**

Rated operational voltage Ue 415 V

Nominal voltage 400 V

Frequency 50/60 Hz

**Electric current**

Rated current 250 A

**Dimensions**

Insertion depth 117 mm

Depth of installed product 135 mm

Internal depth 115 mm

Height of installed product 900 mm

Width of installed product 480 mm

Thickness of sidewall material 1.2 mm

**Cover, door**

Interlockable No

Number of keylock of the door 1

Transparent cover or door No

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

**Connection**

Number of accessible phases 36

**Equipment**

With energy meter No

Quantity of rails 1

Can be accessorized Yes

With bell transformer	No
Extension possible	Yes
With socket	No
<b>Safety</b>	
IK protection code against mechanical impacts	05
Protection class	isol.class I
Glow wire test	according to AS/NZS 61439-1