



JVC4800S16TW



250A TPN board, INVICTA, 48P Chassis , ISO-STD-GR

Technical properties

Architecture

Number of poles of the main switch 3

Functions

Overvoltage protection No

Configuration

Number of modules 16

Main electrical features

Rated operational voltage Ue 415 V

Nominal voltage 400 V

Frequency 50/60 Hz

Electric current

Rated current 160 A

Dimensions

Insertion depth 117 mm

Depth of installed product 135 mm

Internal depth 115 mm

Height of installed product 1000 mm

Width of installed product 480 mm

Thickness of sidewall material 1.2 mm

Cover, door

Interlockable No

Number of keylock of the door 1

Transparent cover or door No

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Connection

Number of accessible phases 48

Equipment

With energy meter No

Quantity of rails 1

Can be accessorized Yes

With bell transformer	No
Extension possible	Yes
With socket	No
Safety	
IK protection code against mechanical impacts	05
Protection class	isol.class I
Glow wire test	according to AS/NZS 61439-1