



KB163N

Insulated busbar 1P 63A prong 10mm² blue 13M

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	13
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	228 mm
Pitch	17.8 mm
Fixation distance in module steps	1

Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Suitable for product with neutral busbar	No
--	----

Equipment

Number of appliances to build in	13
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Insulated	Yes
-----------	-----