



KB181G1

## Insulated prong busbar 1P 80A 16mm<sup>2</sup> 9C for RCBO

### Technical properties

#### Architecture

Number of poles	1 P
-----------------	-----

#### Configuration

Number of modules	13
-------------------	----

#### Voltage

Rated impulse withstand voltage	4 kV
---------------------------------	------

#### Electric current

Rated current	80 A
---------------	------

#### Dimensions

Length	228 mm
--------	--------

Pitch	17.8 mm
-------	---------

#### Power

Total power loss under IN	1.2 W
---------------------------	-------

#### Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Connection cross-sect. rigid cable	16mm <sup>2</sup>
------------------------------------	-------------------

Suitable for product with neutral busbar	No
--	----

Connector type	busbar prong
----------------	--------------

#### Equipment

Number of connections	9 C
-----------------------	-----

Number of appliances to build in	13
----------------------------------	----

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

