



Insulated busbar 1P 100A fork 20mm² 57M

Technical properties

Architecture

Number of poles 1 P

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 415 V

Voltage

Max operating voltage 230 V

Electric current

Rated current 100 A

Dimensions

Length 1000 mm

Pitch 17.8 mm

Fixation distance in module steps 1

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 20mm²

Suitable for product with neutral busbar No

Connector type busbar fork

Type of connection with screw

Equipment

Number of appliances to build in 57

Standards

European directive WEEE not concerned

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Insulated Yes

KD190B