



KDN180G

## Insulated busbar 1P 80A fork 16mm<sup>2</sup> 18M

### Technical properties

#### Architecture

Number of poles 1 P

#### Configuration

Number of modules 18

#### Voltage

Rated impulse withstand voltage 4 kV

#### Electric current

Rated current 80 A

#### Dimensions

Length 319 mm

Pitch 17.8 mm

#### Power

Total power loss under IN 2.4 W

#### Power supply

Number of phases for the power supply 1 phase

#### Installation, mounting

Suitable to a device with an auxiliary No

#### Connection

Connection cross-sect. rigid cable 16mm<sup>2</sup>

Suitable for product with neutral busbar No

Connector type busbar fork

#### Equipment

Number of connections 18 C

Number of appliances to build in 18

#### Standards

European directive RoHS voluntary compliance

#### Safety

Halogen free No

#### Use conditions

Insulated Yes