



KF82A

**Cable terminal 1P prong 2 cables 16mm<sup>2</sup>**

**Technical properties**

**Architecture**

|                 |         |
|-----------------|---------|
| Number of poles | 1 P     |
| Fixing mode     | Screwed |

**Functions**

|  |    |
|--|----|
| Suitable for fine strand conductors                                | No |
| Suitable for fine strand conductors without cable end sleeve       | No |
| Suitable for extra fine-strand conductors                          | No |
| Suitable for extra fine-strand conductors without cable end sleeve | No |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Materials**

|          |                 |
|----------|-----------------|
| Material | Mixed materials |
|----------|-----------------|

**Connection**

|   |                     |
|---|---------------------|
| Connection cross-sect. flexible conductor | 2x10mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 2x16mm <sup>2</sup> |
| Terminal cross-section                    | 16 mm <sup>2</sup>  |
| Type of connection                        | with screw          |

**Accessories included**

|                   |                  |
|-------------------|------------------|
| Type of accessory | Connection clamp |
|-------------------|------------------|

**Equipment**

|                   |   |
|-------------------|---|
| Number of outputs | 1 |
| Number of inputs  | 1 |

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | No  |
| RoHS conform  | Yes |
| Halogen free  | Yes |