



KF83D

## Connection terminal 1P prong 1x35mm<sup>2</sup>

### Technical properties

#### Architecture

Number of poles	1 P
Fixing mode	Screwed

#### Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

#### Voltage

Max operating voltage	500 V
-----------------------	-------

#### Electric current

Rated current	100 A
---------------	-------

#### Materials

Material	Mixed materials
----------	-----------------

#### Connection

Terminal cross-section	35 mm <sup>2</sup>
------------------------	--------------------

#### Accessories included

Type of accessory	Connection clamp
-------------------	------------------

#### Equipment

Number of outputs	0
Number of inputs	1

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-5...60 °C
Storage/transport temperature	-25...80 °C