



KF83D

Connection terminal 1P prong 1x35mm²

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Functions

| | |
|--|----|
| Suitable for fine strand conductors | No |
| Suitable for fine strand conductors without cable end sleeve | No |
| Suitable for extra fine-strand conductors | No |
| Suitable for extra fine-strand conductors without cable end sleeve | No |

Voltage

| | |
|-----------------------|-------|
| Max operating voltage | 500 V |
|-----------------------|-------|

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Connection

| | |
|---|--------------------|
| Connection cross-sect. flexible conductor | 25mm ² |
| Connection cross-sect. rigid cable | 35mm ² |
| Terminal cross-section | 35 mm ² |
| Type of connection | with screw |

Equipment

| | |
|-------------------|---|
| Number of outputs | 0 |
| Number of inputs | 1 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -5...60 °C |
| Storage/transport temperature | -25...80 °C |