



KN14N

Terminal, QuickConnect, neutral, 14 connections

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Functions

Suitable for flexible core	Yes
----------------------------	-----

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	34 mm
Height of installed product	33 mm
Width of installed product	60 mm

Materials

Copper weight of the product	0.015 kg
------------------------------	----------

Connection

Conductor cross-section (flexible), with wire end sleeve	1.5...25 mm ²
Conductor cross-section (rigid)	1.5...25 mm ²

Settings

terminal type	N terminal
---------------	------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No