



KN22E

Terminal,QuickConnect,earth,22 connections

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Functions

| | |
|----------------------------|-----|
| Suitable for flexible core | Yes |
|----------------------------|-----|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 230 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 34 mm |
| Height of installed product | 33 mm |
| Width of installed product | 90 mm |

Materials

| | |
|------------------------------|----------|
| Copper weight of the product | 0.021 kg |
|------------------------------|----------|

Connection

| | |
|--|--------------------------|
| Conductor cross-section (flexible), with wire end sleeve | 1.5...25 mm ² |
| Conductor cross-section (rigid) | 1.5...25 mm ² |

Settings

| | |
|---------------|-------------|
| terminal type | PE terminal |
|---------------|-------------|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |