



KN22P

Terminal,QuickConnect,phase,22 connections

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole | 1 P |

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 230 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 34 mm |
| Height of installed product | 33 mm |
| Width of installed product | 90 mm |

Materials

| | |
|------------------------------|----------|
| Copper weight of the product | 0.021 kg |
|------------------------------|----------|

Settings

| | |
|---------------|----------------|
| terminal type | Phase terminal |
|---------------|----------------|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | Yes |